

# SK 3,5/2,8:FORTL.ZAHLEN 51-60 - Marker card



0804073:0051

<https://www.phoenixcontact.com/us/products/0804073:0051>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker card, Sheet, white, printed horizontally: consecutive numbers from 51 ... 60, mounting type: adhesive, for terminal block width: 3.5 mm, Number of individual labels: 14, text field height: 2.8 mm, text field width: 3.5 mm

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0804073:0051  |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BG05          |
| Product key                          | BG2123        |
| GTIN                                 | 4017918494216 |
| Weight per piece (including packing) | 0.7 g         |
| Weight per piece (excluding packing) | 0.7 g         |
| Customs tariff number                | 49119900      |
| Country of origin                    | PL            |

## Technical data

### Product properties

|              |               |
|--------------|---------------|
| Product type | Klemmenmarker |
| Pitch        | 3.5 mm        |

### Marking

|                             |                                    |
|-----------------------------|------------------------------------|
| Number of individual labels | 14                                 |
| Number of marker strips     | 14                                 |
| Printing direction          | printed horizontally               |
| Printing                    | consecutive numbers from 51 ... 60 |

### Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

### Material specifications

|          |                  |
|----------|------------------|
| Color    | white (RAL 9010) |
| Material | Polyester        |

### Environmental and real-life conditions

#### Ambient conditions

|                                                     |                   |
|-----------------------------------------------------|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

### Dimensions

|        |        |
|--------|--------|
| Width  | 3.5 mm |
| Height | 2.8 mm |
| Pitch  | 3.5 mm |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

# SK 3,5/2,8:FORTL.ZAHLEN 51-60 - Marker card



0804073:0051

<https://www.phoenixcontact.com/us/products/0804073:0051>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000761 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)