


CF 500/DIE RCT 10-2 - Crimp insert



1212246

<https://www.phoenixcontact.com/us/products/1212246>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die for CF 500 automatic crimping device, for tubular cable lugs 4 mm² ... 10 mm², **4 mm²**: outer Ø 5 mm, inner Ø 3 mm, **6 mm²**: outer Ø 6.5 mm, inner Ø 3.8 mm, **10 mm²**: outer Ø 6 mm, inner Ø 4.5 mm

Product description

Outside/inside Ø (mm): **4 mm²**: 5/3; **6 mm²**: 5.5/3.8; **10 mm²**: 6/4.5

Commercial data

Item number	1212246
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH323Z
GTIN	4046356450041
Weight per piece (including packing)	65.2 g
Weight per piece (excluding packing)	65.2 g
Customs tariff number	84799070
Country of origin	DE

CF 500/DIE RCT 10-2 - Crimp insert



1212246

<https://www.phoenixcontact.com/us/products/1212246>

Technical data

Product properties

Product type	Die
Compression	Indent crimp

Connection data

Conductor connection

Cross section range, metric	4 mm ² ... 10 mm ²
-----------------------------	--

Material specifications

Color	silver
-------	--------

Cable/line

External cable diameter	2.4 mm ... 3.7 mm
-------------------------	-------------------

CF 500/DIE RCT 10-2 - Crimp insert



1212246

<https://www.phoenixcontact.com/us/products/1212246>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212246>



EAC

Approval ID: RU C-DE.AI30.B.01549

CF 500/DIE RCT 10-2 - Crimp insert



1212246

<https://www.phoenixcontact.com/us/products/1212246>

Classifications

ECLASS

ECLASS-15.0	17130192
ECLASS-13.0	17130192

ETIM

ETIM 9.0	EC002778
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CF 500/DIE RCT 10-2 - Crimp insert



1212246
<https://www.phoenixcontact.com/us/products/1212246>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com