

CF 3000-TOOLKIT 0,25 - Conversion kit




1212376

<https://www.phoenixcontact.com/us/products/1212376>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Extension kit, complete, for CF 3000, for taped insulated ferrules, 0.25/0.34 mm², sleeve length 8 mm



Product description

Extension kit, 0.25/0.34 mm²

Your advantages

- Suitable for class 2 and class 5 PVC conductors (H05V-K/H07V-K).
Conductors with special insulating material and stranding can only be processed to a limited degree and with reservations.

Commercial data

Item number	1212376
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH323Z
GTIN	4046356461467
Weight per piece (including packing)	426 g
Weight per piece (excluding packing)	373.2 g
Customs tariff number	84799070
Country of origin	DE

CF 3000-TOOLKIT 0,25 - Conversion kit



1212376

<https://www.phoenixcontact.com/us/products/1212376>

Technical data

Product properties

Product type	Conversion kit
Compression	Trapezoidal crimp
Conductor type	PVC

Connection data

Conductor cross-section flexible	0.25 mm ² ... 0.34 mm ²
----------------------------------	---

CF 3000-TOOLKIT 0,25 - Conversion kit



1212376

<https://www.phoenixcontact.com/us/products/1212376>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212376>



EAC

Approval ID: RU C-DE.AI30.B.01549

CF 3000-TOOLKIT 0,25 - Conversion kit



1212376

<https://www.phoenixcontact.com/us/products/1212376>

Classifications

ECLASS

ECLASS-13.0	17130192
ECLASS-15.0	17130192

ETIM

ETIM 9.0	EC002778
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CF 3000-TOOLKIT 0,25 - Conversion kit



1212376
<https://www.phoenixcontact.com/us/products/1212376>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com