

ZB 3,5:UNBEDRUCKT - Zack marker strip



0829414

<https://www.phoenixcontact.com/in/products/0829414>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 3.5 mm, Number of individual labels: 10, text field height: 10.5 mm, text field width: 3.5 mm

Your advantages

- Other pitches available on request
- The multi-section marking strips are easy to fit and can be easily separated if required
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves
- Unmarked marking strips can be custom-labeled with a plotter or by hand

Commercial data

Item number	0829414
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2
Product key	BG2112
GTIN	4046356554152
Weight per piece (including packing)	0.994 g
Weight per piece (excluding packing)	0.95 g
Customs tariff number	39269097
Country of origin	DE

ZB 3,5:UNBEDRUCKT - Zack marker strip



0829414

<https://www.phoenixcontact.com/in/products/0829414>

Technical data

Notes

General	Can be labeled with CMS
General	Can be labeled with CMS

Product properties

Product type	Klemmenmarker
Pitch	3.5 mm

Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10

Dimensions

Width	3.50 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	3.5 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations


Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

Drawings

Schematic diagram



ZB 3,5:UNBEDRUCKT - Zack marker strip



0829414

<https://www.phoenixcontact.com/in/products/0829414>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 3,5:UNBEDRUCKT - Zack marker strip



0829414
<https://www.phoenixcontact.com/in/products/0829414>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.007 kg CO2e

ZB 3,5:UNBEDRUCKT - Zack marker strip

0829414

<https://www.phoenixcontact.com/in/products/0829414>




Accessories

PLOTMARK - Marking plotter

0804499

<https://www.phoenixcontact.com/in/products/0804499>

Marking plotter for the entire portfolio of UC marking materials and materials in sheet and strip format.




CMS-P1-PLOTTER - Marking plotter

5144615

<https://www.phoenixcontact.com/in/products/5144615>

Marking plotter, weight: 8 kg, length: 0.66 m, width: 440 mm, height: 125 mm, color: silver-colored



ZB 3,5:UNBEDRUCKT - Zack marker strip

0829414

<https://www.phoenixcontact.com/in/products/0829414>



TMP-RIBBON 110 YE 100 - Ink ribbon cartridge

0803379

<https://www.phoenixcontact.com/in/products/0803379>

Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., roll length: 60 m, width: 110 mm



STP 3,5-2 - Marker carriers

0830131

<https://www.phoenixcontact.com/in/products/0830131>



Marker carriers, snaps into the PTTB 1,5/S Push-in double-level terminal block, can be marked with UCT-TM 3,5, UCT-TMF 3,5, ZB 3,5, or ZBF 3,5, gray, unmarked, mounting type: plug in, text field height: 10.5 mm, text field width: 3.5 mm

ZB 3,5:UNBEDRUCKT - Zack marker strip



0829414

<https://www.phoenixcontact.com/in/products/0829414>

STP 3,5-3 - Marker carriers

0830132

<https://www.phoenixcontact.com/in/products/0830132>



Marker carriers, snaps into the PT 1,5/S-3L Push-in three-level terminal block, can be marked with UCT-TM 3,5, UCT-TMF 3,5, ZB 3,5, or ZBF 3,5, gray, unmarked, mounting type: plug in, text field height: 10.5 mm, text field width: 3.5 mm

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in