

CRIMPFOX-RCI 6-1 CUS - Crimping pliers



1212775

<https://www.phoenixcontact.com/us/products/1212775>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, laser marked according to customer specifications, for insulated cable lugs, 0.5 mm² ... 6.0 mm² (red, blue, yellow), oval crimp, asymmetrical

Your advantages

- CRIMPFOX-RCI 6 /... represent the top end of the range for cable lug crimping pliers
- Precision-manufactured dies ensure consistently high levels of quality during contact processing

Commercial data

Item number	1212775
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BH313V
GTIN	4046356943024
Weight per piece (including packing)	680.47 g
Weight per piece (excluding packing)	680.47 g
Country of origin	SE

CRIMPFOX-RCI 6-1 CUS - Crimping pliers



1212775

<https://www.phoenixcontact.com/us/products/1212775>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Crimping tool

Compression

Oval crimp

Crimping position 1

Min. cross section

0.5 mm²

Max. cross section

1.5 mm²

AWG min

20

AWG max

16

Crimping position 2

Min. cross section

1.5 mm²

Max. cross section

2.5 mm²

AWG min

16

AWG max

14

Crimping position 3

Min. cross section

4 mm²

Max. cross section

6 mm²

AWG min

12

AWG max

10

Connection data

Conductor connection

Cross section range, metric

0.5 mm² ... 6 mm²

Cross section range AWG

20 ... 10

Dimensions

Width

25 mm

Height

68 mm

Length

256 mm

Material specifications

Color

black

CRIMPFOX-RCI 6-1 CUS - Crimping pliers



1212775

<https://www.phoenixcontact.com/us/products/1212775>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212775>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-RCI 6-1 CUS - Crimping pliers



1212775

<https://www.phoenixcontact.com/us/products/1212775>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-RCI 6-1 CUS - Crimping pliers



1212775
<https://www.phoenixcontact.com/us/products/1212775>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com