

UBE + ES/KMK 3 - Marker carriers



1004089

<https://www.phoenixcontact.com/us/products/1004089>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker carriers, for the identification of terminal block groups, for E/UK end bracket or E/U end bracket, with 40 x 17 mm perforated insert strip, gray, unmarked, perforated, mounting type: latching, text field height: 17 mm, text field width: 40 mm

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1004089 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG12 |
| Product key | BG211A |
| GTIN | 4017918011895 |
| Weight per piece (including packing) | 7.228 g |
| Weight per piece (excluding packing) | 6.57 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

UBE + ES/KMK 3 - Marker carriers



1004089

<https://www.phoenixcontact.com/us/products/1004089>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

Dimensions

| | |
|--------|----------|
| Width | 20.00 mm |
| Height | 42.80 mm |
| Depth | 42.50 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -40 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Mounting

| | |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

UBE + ES/KMK 3 - Marker carriers



1004089

<https://www.phoenixcontact.com/us/products/1004089>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
| ECLASS-15.0 | 27281105 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002248 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UBE + ES/KMK 3 - Marker carriers



1004089

<https://www.phoenixcontact.com/us/products/1004089>

Environmental product compliance

| | |
|---|----------------------------|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
| EF3.0 Climate Change | |
| CO2e kg | 0.03 kg CO2e |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com