

# OCS CORNER SET - Corner attachment



1471789

<https://www.phoenixcontact.com/us/products/1471789>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Corner mount, set of 4 pieces incl. screws for all housing sizes, material: PC-ABS, color: light gray

## Your advantages

- Internationally certified housing system
- Special plastic enables safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

## Commercial data

Item number	1471789
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC04
Product key	ACFDBZ
GTIN	4063151880538
Weight per piece (including packing)	41.233 g
Weight per piece (excluding packing)	0.125 g
Customs tariff number	39269097
Country of origin	EE

# OCS CORNER SET - Corner attachment



1471789

<https://www.phoenixcontact.com/us/products/1471789>

## Technical data

### Notes

Recommendation	Further information and detailed dimensions are available in the download area.
Assembly note	Only use the screws supplied for mounting.

### Product properties

Product type	Select corner
Housing type	Outdoor housing
Housing series	OCS

### Dimensions

Width	25 mm
Height	51 mm
Depth	11 mm

### Material specifications

Color	light gray (RAL 7035)
Material ()	Polycarbonate
Flammability rating according to UL 94	V2
Insulating material	PC
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

### Mounting

Mounting type	Screw mounting
---------------	----------------

### Packaging specifications

Type of packaging	PE bag
-------------------	--------

# OCS CORNER SET - Corner attachment



1471789

<https://www.phoenixcontact.com/us/products/1471789>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1471789>

### FI Cert

Approval ID: FI/42054

# OCS CORNER SET - Corner attachment



1471789

<https://www.phoenixcontact.com/us/products/1471789>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 9.0	EC002779
----------	----------

# OCS CORNER SET - Corner attachment



1471789

<https://www.phoenixcontact.com/us/products/1471789>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: n/a)
SCIP	52818e4b-b440-41f8-9ef2-6a9e1f397811

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)