

CC-AT60-S16-R16/20-AU - Crimp contact



1519755

<https://www.phoenixcontact.com/us/products/1519755>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: AT04, Pin, turned, contact diameter: 1.6 mm, rated current: 13 A, contact material: Cu alloy

Commercial data

Item number	1519755
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF72
Product key	AF2IEB
GTIN	4063151984205
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	0.5 g
Country of origin	MX

CC-AT60-S16-R16/20-AU - Crimp contact



1519755

<https://www.phoenixcontact.com/us/products/1519755>

Technical data

Notes

General	AT60-202-1631
Assembly note	Crimp with 8-indent crimp tool qualified to MIL-DTL-22520/1, e.g., Daniels AF8-TH1A or Rennsteig 8758 0000 6 (tool) /8758 1102 0 (Multi pin locator)
Trade restriction	
CE note	The products are offered exclusively for export outside the EU and the European Economic Area.

Product properties

Product type	Crimp contact
Series	AT04
	AHD10-9
Contact material type	turned


Connection data

Connection technology	
Contact connection type	Pin

Material specifications

Material Contact	Cu alloy
Material Contact surface	Au

Dimensions

Dimensional drawing	
Diameter (Contact diameter)	1.6 mm

Electrical properties

Rated current	13 A (MAX)
---------------	------------

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-55 °C ... 125 °C

CC-AT60-S16-R16/20-AU - Crimp contact


1519755

<https://www.phoenixcontact.com/us/products/1519755>



Drawings

Dimensional drawing



Dimensional drawing

CC-AT60-S16-R16/20-AU - Crimp contact



1519755

<https://www.phoenixcontact.com/us/products/1519755>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

CC-AT60-S16-R16/20-AU - Crimp contact



1519755

<https://www.phoenixcontact.com/us/products/1519755>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com