

# HC-B 48-SMLD-100/O2PG36 - Housing



1460037

<https://www.phoenixcontact.com/us/products/1460037>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Box mounting base, with single locking latch, with protective cover, height: 100 mm, without screw connection, 2 x Pg36

## Commercial data

Item number	1460037
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF7AAC
GTIN	4046356696708
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

# HC-B 48-SMLD-100/O2PG36 - Housing



1460037

<https://www.phoenixcontact.com/us/products/1460037>

## Technical data

### Notes

General	For contact inserts HC-B48, DD216, M
---------	--------------------------------------

### Product properties

Product type	Housing with locking latch
Housing type	Surface mounting housing
Type	B48
No. of cable outlets	2
Type of the screw connection	2x Pg36
Cable outlet	lateral
Pg screw connection	none

### Dimensions

Dimensional drawing	
Width	120 mm
Height	100 mm
Length	145 mm

### Material specifications

Seal material	NBR
Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray
Material, protective cover	PA
Locking latch material	Steel, galvanized

### Mechanical properties

#### Mechanical data

Type of the screw connection	2x Pg36
Locking type	Latch

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65 (When plugged in) IP54 (with closed protective cover)
Ambient temperature (operation)	-40 °C ... 125 °C

# HC-B 48-SMLD-100/O2PG36 - Housing


1460037

<https://www.phoenixcontact.com/us/products/1460037>



## Drawings

Dimensional drawing



Dimensional drawing

# HC-B 48-SMLD-100/O2PG36 - Housing



1460037

<https://www.phoenixcontact.com/us/products/1460037>

## Classifications

### ECLASS

ECLASS-13.0	27440202
-------------	----------

# HC-B 48-SMLD-100/O2PG36 - Housing



1460037

<https://www.phoenixcontact.com/us/products/1460037>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)