

# KGG-MSTB 2,5/ 7 BK - Cable housing



1713973

<https://www.phoenixcontact.com/us/products/1713973>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable housing, color: black, product range: KGG-MSTB 2,5, width: 19 mm

## Commercial data

Item number	1713973
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AAHZDC
GTIN	4055626476704
Weight per piece (including packing)	10.09 g
Weight per piece (excluding packing)	9.919 g
Customs tariff number	39269097
Country of origin	PL

# KGG-MSTB 2,5/ 7 BK - Cable housing



1713973

<https://www.phoenixcontact.com/us/products/1713973>

## Technical data

### Product properties

Product type	Cable housing
Product family	KGG-MSTB 2,5
Number of positions	7
Pitch	0 mm

### Mounting

#### Cable clamp

Tightening torque	0.2 Nm
-------------------	--------

### Material specifications

Color (Housing)	black (RAL 9005)
Flammability rating according to UL 94	HB
Insulating material	ABS
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	HB

### Dimensions

Width	19 mm
Height	37 mm
Pitch	-

# KGG-MSTB 2,5/ 7 BK - Cable housing

1713973

<https://www.phoenixcontact.com/us/products/1713973>



## Classifications

### ECLASS

ECLASS-13.0	27460402
ECLASS-15.0	27460402

### ETIM

ETIM 9.0	EC002943
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# KGG-MSTB 2,5/ 7 BK - Cable housing



1713973

<https://www.phoenixcontact.com/us/products/1713973>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)