

2958587

<https://www.phoenixcontact.com/us/products/2958587>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, DIN rail mounting, Plug-in module base element, with foot element, width: 35 mm, height: 111 mm, depth: 27.7 mm



Commercial data

Item number	2958587
Packing unit	500 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHDDA
GTIN	4017918245184
Weight per piece (including packing)	26.58 g
Weight per piece (excluding packing)	25.3 g
Country of origin	PL

# UM-BEFE 35-1 BU (VPE 500) - Base element



2958587

<https://www.phoenixcontact.com/us/products/2958587>

## Technical data

### Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM BE
Ventilation openings present	no

### Dimensions

Width	35 mm
Height	111 mm
Depth	27.7 mm

### Material specifications

Color (Housing)	blue (RAL 5015)
Housing material	PA
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# UM-BEFE 35-1 BU (VPE 500) - Base element



2958587

<https://www.phoenixcontact.com/us/products/2958587>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2958587>



**UL Recognized**

Approval ID: E240868

# UM-BEFE 35-1 BU (VPE 500) - Base element



2958587

<https://www.phoenixcontact.com/us/products/2958587>

## Classifications

### ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM-BEFE 35-1 BU (VPE 500) - Base element



2958587

<https://www.phoenixcontact.com/us/products/2958587>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)