

BMKL 20X 8 YE - Label sheet, DIN A4




5032138

<https://www.phoenixcontact.com/us/products/5032138>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label sheet, DIN A4, Sheet, yellow, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, Number of individual labels: 224, text field height: 8 mm, text field width: 20 mm



Your advantages

- These labels have been specially developed for laser printers
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- Can be printed on all commercially available laser printers
- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking"
- The unperforated SK-U... sheets are available for custom label designs

Commercial data

Item number	5032138
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG13
Product key	BG2414
GTIN	4017918095703
Weight per piece (including packing)	14.512 g
Weight per piece (excluding packing)	13.8 g
Customs tariff number	39199080
Country of origin	DE

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Marking

Number of individual labels	224
Number of individual labels per row	7
Identification technology	Office laser printing

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Color	yellow (RAL 1018)
Material	Polyester
Base element material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
Recommended ambient temperature (storage/transport)	20 °C ... 25 °C
Recommended humidity (storage/transport)	40 % ... 50 %
Shelf life	2 years

Dimensions

Width	8.00 mm
Height	20.00 mm
Depth	0.09 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Notes

General	Print image may vary depending on laser printer
---------	---

BMKL 20X 8 YE - Label sheet, DIN A4




5032138

<https://www.phoenixcontact.com/us/products/5032138>

Drawings

Dimensional drawing



5032138

<https://www.phoenixcontact.com/us/products/5032138>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

BMKL 20X 8 YE - Label sheet, DIN A4



5032138
<https://www.phoenixcontact.com/us/products/5032138>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com