

ZB 7,62 UV-100 - Zack marker strip



0829029

<https://www.phoenixcontact.com/us/products/0829029>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 7.62 mm, Number of individual labels: 1000, text field height: 10.5 mm, text field width: 10.5 mm

Commercial data

Item number	0829029
Packing unit	10 pc
Minimum order quantity	100 pc
Product key	BG2112
GTIN	4046356538169
Weight per piece (including packing)	1.41 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

ZB 7,62 UV-100 - Zack marker strip



0829029

<https://www.phoenixcontact.com/us/products/0829029>

Technical data

Product properties

Product type	Terminal marking
Pitch	7.62 mm

Marking

Number of individual labels	1000
Number of individual labels per row	10
Number of marker strips	100
Identification technology	Plotter

Dimensions

Width	6.45 mm
Height	10.50 mm
Depth	4.30 mm
Pitch	7.62 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

ZB 7,62 UV-100 - Zack marker strip



0829029

<https://www.phoenixcontact.com/us/products/0829029>

Classifications

ECLASS

ECLASS-13.0	27281101
-------------	----------

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 7,62 UV-100 - Zack marker strip



0829029
<https://www.phoenixcontact.com/us/products/0829029>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com