

# CUTFOX 25 VDE - Cable-cutting tool



1212127

<https://www.phoenixcontact.com/us/products/1212127>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



**Cable cutter**, precision blade with macro-notching, for copper and aluminum up to 70 mm<sup>2</sup>, VDE 1000 V AC/ 1500 V DC tested

## Your advantages

- VDE tested
- Special tool steel for permanent use
- Precision cutting edge with macro-notching
- Adjustable screw joint
- Ergonomically shaped two-component handles for fatigue-free and non-slip use

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212127       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3113        |
| GTIN                                 | 4046356454261 |
| Weight per piece (including packing) | 321.5 g       |
| Weight per piece (excluding packing) | 319.2 g       |
| Customs tariff number                | 82032000      |
| Country of origin                    | DE            |

# CUTFOX 25 VDE - Cable-cutting tool



1212127

<https://www.phoenixcontact.com/us/products/1212127>

## Technical data

### Notes

|                                  |                                                                                                               |
|----------------------------------|---------------------------------------------------------------------------------------------------------------|
| Environmental Product Compliance |                                                                                                               |
| California Proposition 65        | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |

### Product properties

|                  |                                               |
|------------------|-----------------------------------------------|
| Product type     | Cutting tool                                  |
| Application      | Aluminum                                      |
|                  | Copper                                        |
| Product property | Toothed cutting surface with pre-cutting zone |
|                  | Optimized leverage                            |
|                  | Crush-free cutting                            |
|                  | Ergonomic two-component handle                |
|                  | Adjustable screw joint                        |
|                  | VDE tested                                    |

### Dimensions

|          |        |
|----------|--------|
| Length   | 210 mm |
| Diameter | 25 mm  |

External dimensions

|                  |         |
|------------------|---------|
| Outside diameter | ≤ 25 mm |
|------------------|---------|

### Material specifications

|       |              |
|-------|--------------|
| Color | multicolored |
|-------|--------------|

### Cable/line

|                         |            |
|-------------------------|------------|
| External cable diameter | ≤ 25.00 mm |
|-------------------------|------------|

### Standards and regulations

|       |                                  |
|-------|----------------------------------|
| Tests | DIN EN 60900 (VDE 0682 PART 201) |
|       | DIN ISO 5746                     |

# CUTFOX 25 VDE - Cable-cutting tool



1212127

<https://www.phoenixcontact.com/us/products/1212127>

## Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212127>



**EAC**

Approval ID: RU x-DE.xx08.B.02974



**VDE approval of drawings**

Approval ID: 40052526

# CUTFOX 25 VDE - Cable-cutting tool



1212127

<https://www.phoenixcontact.com/us/products/1212127>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21044701 |
| ECLASS-15.0 | 21044701 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000142 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CUTFOX 25 VDE - Cable-cutting tool



1212127  
<https://www.phoenixcontact.com/us/products/1212127>

## Environmental product compliance

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                     |
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
| EU REACH SVHC                           |                                                                                     |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                          |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)