

C-ME 4/1 - Operating lever



1062645

<https://www.phoenixcontact.com/us/products/1062645>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Operating lever, for switching test disconnect terminal blocks on and off

Commercial data

Item number	1062645
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2ZWX
GTIN	4055626718446
Weight per piece (including packing)	0.6 g
Weight per piece (excluding packing)	0.585 g
Customs tariff number	39269097
Country of origin	PL

C-ME 4/1 - Operating lever

1062645

<https://www.phoenixcontact.com/us/products/1062645>



Technical data

Product properties

Product type	Switch module
Number of positions	1

Dimensions

Width	6 mm
Height	5.2 mm
Depth	23.8 mm

Material specifications

Color	orange (RAL 2003)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

C-ME 4/1 - Operating lever

1062645

<https://www.phoenixcontact.com/us/products/1062645>



Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

ETIM

ETIM 9.0	EC002848
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

C-ME 4/1 - Operating lever

1062645

<https://www.phoenixcontact.com/us/products/1062645>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com