

HC-26S1N324100 - Device connector rear mounting



1590378

<https://www.phoenixcontact.com/us/products/1590378>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, straight, M27, contact connection type: Socket, Flat gasket, number of positions: 26, connection method: Solder pins, this item is expected to be lead-free from Q4 2025 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1590378
Packing unit	24 pc
Minimum order quantity	24 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAJR
GTIN	4046356187145
Weight per piece (including packing)	45.508 g
Weight per piece (excluding packing)	41.7 g
Customs tariff number	85366990
Country of origin	DE

HC-26S1N324100 - Device connector rear mounting



1590378

<https://www.phoenixcontact.com/us/products/1590378>

Technical data

Mounting

Mounting type	Rear mounting/square flange (4x M3)
---------------	-------------------------------------

Product properties

Product type	Circular connectors (device side)
Application	Signal
Number of positions	26
Thread type	M27

Material specifications

Flammability rating according to UL 94	V0
----------------------------------------	----

Electrical properties

Contact

Contact diameter	1 mm
Nominal current I_N	8 A
Nominal voltage U_N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Conductor connection

Connection method	Solder pins
Contact connection type	Socket

Connector

Type	straight
Direction of rotation	Standard

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67, when plugged in
----------------------	-----------------------

HC-26S1N324100 - Device connector rear mounting




1590378

<https://www.phoenixcontact.com/us/products/1590378>


Drawings

Dimensional drawing



Dimensional drawing

Schematic diagram



Connector pin assignment

HC-26S1N324100 - Device connector rear mounting



1590378

<https://www.phoenixcontact.com/us/products/1590378>

Classifications

ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

ETIM

ETIM 9.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-26S1N324100 - Device connector rear mounting



1590378

<https://www.phoenixcontact.com/us/products/1590378>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	26f9698b-0558-4d55-9784-82c056f14bb5

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com