

# VS-SI-SD-FR - Socket insert



1656534

<https://www.phoenixcontact.com/us/products/1656534>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ground contact socket, plastic, for France



## Commercial data

Item number	1656534
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF70
Product key	AF7EBX
GTIN	4046356029902
Weight per piece (including packing)	161.2 g
Weight per piece (excluding packing)	154.2 g
Customs tariff number	85366990
Country of origin	BE

# VS-SI-SD-FR - Socket insert



1656534

<https://www.phoenixcontact.com/us/products/1656534>

## Technical data

### Product properties

Product type	Socket
Country ID	France


### Electrical properties

Rated voltage (III/3)	250 V
Rated current	16 A

### Connection data

Connection method	Screw connection
-------------------	------------------

### Dimensions

Dimensional drawing	
Width	51 mm
Height	88 mm
Depth	68 mm

### Material specifications

Material Housing	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 60 °C

### Mounting

Assembly note	suitable for all mounting frames
---------------	----------------------------------

# VS-SI-SD-FR - Socket insert


1656534

<https://www.phoenixcontact.com/us/products/1656534>



## Drawings

Dimensional drawing



Socket insert

# VS-SI-SD-FR - Socket insert



1656534

<https://www.phoenixcontact.com/us/products/1656534>

## Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1656534>



**EAC**

Approval ID: RU C-DE.A\*30.B.01102

# VS-SI-SD-FR - Socket insert



1656534

<https://www.phoenixcontact.com/us/products/1656534>

## Classifications

### ECLASS

ECLASS-15.0	27144021
ECLASS-13.0	27144021

### ETIM

ETIM 9.0	EC000450
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-SI-SD-FR - Socket insert



1656534

<https://www.phoenixcontact.com/us/products/1656534>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f011b060-3b8a-4d90-ad15-b28cda40d4ca

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)