

PSR-CONF-WIN1.0 - Configuration and diagnostic software



2981554

<https://www.phoenixcontact.com/us/products/2981554>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Configuration software for parameterizing the PSR-RSM4 safe downtime and over-speed safety relay, with programming cable

Commercial data

Item number	2981554
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN01
Product key	DNA243
GTIN	4017918996840
Weight per piece (including packing)	165.8 g
Weight per piece (excluding packing)	165.8 g
Customs tariff number	85234910
Country of origin	DE

PSR-CONF-WIN1.0 - Configuration and diagnostic software



2981554

<https://www.phoenixcontact.com/us/products/2981554>

Technical data

Product properties

Product type	Configuration and diagnostics
Scope of supply	PSR configuration software with connecting cable
Basic functions	Configuration software for PSR-RSM4 safe downtime and over-speed safety relay

System properties

Type of software	Embedded
Intended use for the software	Configuration

License information

Type of license	Freeware
-----------------	----------

Functionality

Basic functions	Configuration software for PSR-RSM4 safe downtime and over-speed safety relay
-----------------	---

System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® 7 (32-Bit/64-Bit)
	Windows XP
	MS Windows NT 4.0 with Service Pack > 4, MS Windows 2000 and MS Windows XP
	Windows 98, Windows 2000, Windows XP
Processor	Pentium, 2 GHz (recommended), 1 GHz (min.)
Hard disk memory	min. 250 Mbyte (Free hard disk memory space)
RAM	1 GByte (under Windows 7/under Windows XP: 512 Mbytes (min.))
Languages supported	German, English, French, Spanish, Italian
Optical drive	CD-ROM
Screen resolution	800x600

Classifications

ECLASS

ECLASS-13.0	27242501
-------------	----------

ETIM

ETIM 9.0	EC000809
----------	----------

UNSPSC

UNSPSC 21.0	43233600
-------------	----------

2981554

<https://www.phoenixcontact.com/us/products/2981554>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com