

# UM108-SE-A73 - Lateral element

2959751

<https://www.phoenixcontact.com/us/products/2959751>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Side element, without foot, tall version, for 73 mm wide U-shaped cover.



## Commercial data

Item number	2959751
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDBA
GTIN	4017918086367
Weight per piece (including packing)	16 g
Weight per piece (excluding packing)	16 g
Customs tariff number	39269097
Country of origin	PL

# UM108-SE-A73 - Lateral element

2959751

<https://www.phoenixcontact.com/us/products/2959751>



## Technical data

### Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM108
Ventilation openings present	no

### Dimensions

Dimensional drawing	
Depth	125 mm

### Material specifications

Color (Housing)	green (RAL 6021)
Flammability rating according to UL 94	V0
Housing material	PA
Surface characteristics	untreated

### Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)


# UM108-SE-A73 - Lateral element

2959751

<https://www.phoenixcontact.com/us/products/2959751>



## Drawings



# UM108-SE-A73 - Lateral element



2959751

<https://www.phoenixcontact.com/us/products/2959751>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2959751>



**UL Recognized**

Approval ID: E240868

# UM108-SE-A73 - Lateral element



2959751

<https://www.phoenixcontact.com/us/products/2959751>

## Classifications

### ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM108-SE-A73 - Lateral element



2959751  
<https://www.phoenixcontact.com/us/products/2959751>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)