

# WP-SC BRASS 36 - Cable protection end sleeve



3241070

<https://www.phoenixcontact.com/us/products/3241070>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable protection end sleeve, material: Brass, nickel-plated, color: silver-colored, inside diameter: 29.5 mm

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3241070       |
| Packing unit                         | 25 pc         |
| Minimum order quantity               | 25 pc         |
| Sales key                            | BF68          |
| Product key                          | AF7DSA        |
| GTIN                                 | 4046356711920 |
| Weight per piece (including packing) | 15.016 g      |
| Weight per piece (excluding packing) | 13.5 g        |
| Customs tariff number                | 74122000      |
| Country of origin                    | DE            |

# WP-SC BRASS 36 - Cable protection end sleeve



3241070

<https://www.phoenixcontact.com/us/products/3241070>

## Technical data

### Product properties

|              |                |
|--------------|----------------|
| Product type | Protective cap |
|--------------|----------------|

### Dimensions

|          |       |
|----------|-------|
| Diameter | 36 mm |
|----------|-------|

#### Internal dimensions

|                   |         |
|-------------------|---------|
| Internal diameter | 29.5 mm |
|-------------------|---------|

### Material specifications

|            |                      |
|------------|----------------------|
| Material   | Brass, nickel-plated |
| Components | halogen-free         |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 250 °C |
|---------------------------------|-------------------|

# WP-SC BRASS 36 - Cable protection end sleeve



3241070

<https://www.phoenixcontact.com/us/products/3241070>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27430316 |
| ECLASS-15.0 | 27430316 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000519 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# WP-SC BRASS 36 - Cable protection end sleeve



3241070

<https://www.phoenixcontact.com/us/products/3241070>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 8c7199b4-beca-4b40-9d0a-5369e16c9e3b |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)