

FL DIN-RAIL ADAPTER 40 - Mounting panel



1085484

<https://www.phoenixcontact.com/us/products/1085484>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The FL DIN-RAIL ADAPTER 40 is designed to allow products 40 mm wide to be mounted flush to a standard 35 mm DIN rail, in any orientation.

Product description

The FL DIN-RAIL ADAPTER 40 is designed to allow products 40 mm wide to be mounted flush to a standard 35 mm DIN rail, in any orientation.

Your advantages

- Easy and secure adapting of DIN rail products to mount flush to a DIN rail

Commercial data

Item number	1085484
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN22
Product key	DNN1ZZ
GTIN	4055626874104
Weight per piece (including packing)	152.366 g
Weight per piece (excluding packing)	95.45 g
Customs tariff number	73269098
Country of origin	TW

FL DIN-RAIL ADAPTER 40 - Mounting panel



1085484

<https://www.phoenixcontact.com/us/products/1085484>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Assembly adapter
--------------	------------------

Dimensions

Width	34 mm
Height	104.21 mm
Depth	55.8 mm
Hole diameter	5 mm

Material specifications

Material	Stainless steel 304
Housing material	Stainless steel

FL DIN-RAIL ADAPTER 40 - Mounting panel



1085484

<https://www.phoenixcontact.com/us/products/1085484>

Classifications

ECLASS

ECLASS-13.0	27182807
ECLASS-15.0	27182807

ETIM

ETIM 9.0	EC002625
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

FL DIN-RAIL ADAPTER 40 - Mounting panel



1085484
<https://www.phoenixcontact.com/us/products/1085484>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com