

CRIMPFOX CENTRUS 6S SET - Tool set



1213999

<https://www.phoenixcontact.com/us/products/1213999>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cutting, stripping, and crimping set, packaged in a tool case, comprising CUTFOX 18, WIREFOX 10, CRIMPFOX CENTRUS 6S, AI SORTI BOX RD, TOOL-KIT STANDARD EMPTY

Product description

Tool set, equipped

Your advantages

- Universal tools sets with WIREFOX 10, CRIMPFOX-CENTRUS tools from TOOL fox
- Rugged and heavy-duty tool bags
- Ideal for TWIN ferrule

Commercial data

Item number	1213999
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3521
GTIN	4055626212715
Weight per piece (including packing)	1,372.8 g
Weight per piece (excluding packing)	1,355 g
Customs tariff number	82060000
Country of origin	SE

CRIMPFOX CENTRUS 6S SET - Tool set



1213999

<https://www.phoenixcontact.com/us/products/1213999>

Set consists of

CRIMPFOX CENTRUS 6S - Crimping pliers

1213144

<https://www.phoenixcontact.com/us/products/1213144>



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

AI SORTI BOX RD - Assortment box

3202960

<https://www.phoenixcontact.com/us/products/3202960>



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

CRIMPFOX CENTRUS 6S SET - Tool set

1213999

<https://www.phoenixcontact.com/us/products/1213999>



WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



Stripping tool, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

TOOL-KIT STANDARD EMPTY - Toolbag, unequipped

1212423

<https://www.phoenixcontact.com/us/products/1212423>



Tool box, unequipped

CRIMPFOX CENTRUS 6S SET - Tool set

1213999

<https://www.phoenixcontact.com/us/products/1213999>



CUTFOX 18 - Cable-cutting tool

1212129

<https://www.phoenixcontact.com/us/products/1212129>



Cable cutter, angled, for copper and aluminum up to 18 mm diameter (up to 50 mm²)

CRIMPFOX CENTRUS 6S SET - Tool set



1213999

<https://www.phoenixcontact.com/us/products/1213999>

Technical data

Notes

General	DIN 46228-1, DIN 46228-4, UL 486F, Form A, E, F
Environmental Product Compliance	
California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Tool set
Type of packaging	Bag
Compression	Square crimp

Dimensions

Width	65 mm
Height	315 mm
Length	165 mm

Material specifications

Color	black (RAL 9005)
-------	------------------

CRIMPFOX CENTRUS 6S SET - Tool set



1213999

<https://www.phoenixcontact.com/us/products/1213999>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1213999>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX CENTRUS 6S SET - Tool set



1213999

<https://www.phoenixcontact.com/us/products/1213999>

Classifications

ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

ETIM

ETIM 9.0	EC000149
----------	----------

UNSPSC

UNSPSC 21.0	27113200
-------------	----------

CRIMPFOX CENTRUS 6S SET - Tool set



1213999
<https://www.phoenixcontact.com/us/products/1213999>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com