

ES/KMK 3-GB - Insert strip

1005088

<https://www.phoenixcontact.com/us/products/1005088>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert strip, Sheet, white, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: insert, Number of individual labels: 52, text field height: 17.2 mm, text field width: 39.75 mm



Commercial data

Item number	1005088
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG12
Product key	BG2312
GTIN	4017918012397
Weight per piece (including packing)	10.25 g
Weight per piece (excluding packing)	10.029 g
Customs tariff number	48025890
Country of origin	DE

ES/KMK 3-GB - Insert strip

1005088

<https://www.phoenixcontact.com/us/products/1005088>



Technical data

Notes

General	Print image may vary depending on laser printer
---------	---

Product properties

Product type	Klemmenmarker
--------------	---------------

Marking

Number of individual labels	52
Number of individual labels per row	4

Dimensions

Width	39.55 mm
Height	17.20 mm
Depth	0.17 mm

Material specifications

Color	white (RAL 9010)
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Mounting

Mounting type	insert
---------------	--------

ES/KMK 3-GB - Insert strip

1005088

<https://www.phoenixcontact.com/us/products/1005088>



Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

ES/KMK 3-GB - Insert strip

1005088

<https://www.phoenixcontact.com/us/products/1005088>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com