

# KV-DI-PG16-1XASI - Seal

1582462

<https://www.phoenixcontact.com/us/products/1582462>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Seal for one AS-i line, 17.2 x 9 mm, from NBR, black, for IP65/67 degree of protection



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1582462       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BF50          |
| Product key                          | AF6ZBX        |
| GTIN                                 | 4046356463102 |
| Weight per piece (including packing) | 2.51 g        |
| Weight per piece (excluding packing) | 2.48 g        |
| Customs tariff number                | 40169300      |
| Country of origin                    | DE            |

# KV-DI-PG16-1XASI - Seal

1582462

<https://www.phoenixcontact.com/us/products/1582462>



## Technical data

### Product properties

|              |      |
|--------------|------|
| Product type | Seal |
|--------------|------|

### Material specifications

|               |     |
|---------------|-----|
| Seal material | NBR |
|---------------|-----|

### Environmental and real-life conditions

#### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Degree of protection                    | IP65             |
|                                         | IP67             |
| Ambient temperature (operation)         | -40 °C ... 80 °C |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Ambient temperature (assembly)          | -5 °C ... 40 °C  |

# KV-DI-PG16-1XASI - Seal



1582462

<https://www.phoenixcontact.com/us/products/1582462>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440192 |
| ECLASS-15.0 | 27440192 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002943 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# KV-DI-PG16-1XASI - Seal

1582462

<https://www.phoenixcontact.com/us/products/1582462>



## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)