

CF 1000-TOOLKIT 0,34/ 8 - Conversion kit



1208225

<https://www.phoenixcontact.com/us/products/1208225>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Installation kit for CF 1000-1,5 up to serial number 160591, for insulated ferrules in accordance with DIN46228-4: 2017-05, cross section range: 0.25-0.34 mm², AWG 24-22, stripping length: 8 mm

Commercial data

Item number	1208225
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH323Z
GTIN	4046356011372
Weight per piece (including packing)	1,620 g
Weight per piece (excluding packing)	1,620 g
Customs tariff number	84799070
Country of origin	DE

CF 1000-TOOLKIT 0,34/ 8 - Conversion kit

1208225

<https://www.phoenixcontact.com/us/products/1208225>



Technical data

Product properties

Product type	Conversion kit
Compression	Trapezoidal crimp

Connection data

Conductor cross-section flexible	0.25 mm ² ... 0.34 mm ²
----------------------------------	---

CF 1000-TOOLKIT 0,34/ 8 - Conversion kit

1208225

<https://www.phoenixcontact.com/us/products/1208225>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1208225>



EAC

Approval ID: RU C-DE.AI30.B.01549

CF 1000-TOOLKIT 0,34/ 8 - Conversion kit



1208225

<https://www.phoenixcontact.com/us/products/1208225>

Classifications

ECLASS

ECLASS-13.0	17130192
ECLASS-15.0	17130192

ETIM

ETIM 9.0	EC002778
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CF 1000-TOOLKIT 0,34/ 8 - Conversion kit



1208225

<https://www.phoenixcontact.com/us/products/1208225>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com