

CRIMPFOX CENTRUS 6H CUS - Crimping pliers



1213166

<https://www.phoenixcontact.com/us/products/1213166>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, laser-inscribed to customer specifications, pliers and properties as in CRIMPFOX CENTRUS 6H

Your advantages

- Pressure lock ensures consistently high quality crimping results
- Ergonomic handle design ensures comfortable, fatigue-free handling
- With a particularly small handle width, the tool fits perfectly in your hand
- Up to 30 % lower actuation force, thanks to optimized leverage
- Ideal for TWIN ferrule
- Sturdy plastic guard over the head of the pliers protects the tool against damage caused by dropping

Commercial data

Item number	1213166
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BH313V
GTIN	4055626212708
Weight per piece (including packing)	472.8 g
Weight per piece (excluding packing)	472 g
Country of origin	SE

CRIMPFOX CENTRUS 6H CUS - Crimping pliers



1213166

<https://www.phoenixcontact.com/us/products/1213166>

Technical data

Notes

General	DIN 46228-1, DIN 46228-4
Environmental Product Compliance	
California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	HEX crimp

Crimping position 1

Min. cross section	0.14 mm ²
Max. cross section	6 mm ²
AWG min	26
AWG max	10

Connection data

Conductor connection

Cross section range, metric	0.14 mm ² ... 6 mm ²
Cross section range AWG	26 ... 10

Dimensions

Width	70 mm
Height	21 mm
Length	180 mm

Material specifications

Color	black/green
-------	-------------

CRIMPFOX CENTRUS 6H CUS - Crimping pliers



1213166

<https://www.phoenixcontact.com/us/products/1213166>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1213166>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX CENTRUS 6H CUS - Crimping pliers



1213166

<https://www.phoenixcontact.com/us/products/1213166>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX CENTRUS 6H CUS - Crimping pliers



1213166
<https://www.phoenixcontact.com/us/products/1213166>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com