

RC-1RS1NRA0000 - Contact insert

1603213

<https://www.phoenixcontact.com/us/products/1603213>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 16+2+FE, contact connection type: Socket, Crimp connection, series: NC, RC, RM, TU, UC

Commercial data

Item number	1603213
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAFT
GTIN	4046356244176
Weight per piece (including packing)	2.63 g
Weight per piece (excluding packing)	2.54 g
Customs tariff number	85389099
Country of origin	DE

RC-1RS1NRA0000 - Contact insert



1603213

<https://www.phoenixcontact.com/us/products/1603213>

Technical data

Notes

Order information:	Order crimp contacts 16 x Ø 1 mm, 2 x Ø 1.5 mm, 1 x Ø 1.5 (PE) separately
--------------------	---

Product properties

Product type	Contact insert
Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	19
Connection profile	16+2+FE
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	1.5 mm
Nominal current I_N	10 A (for max. connection cross section)
Nominal voltage U_N	48 V AC
	74 V DC
Overvoltage category	II
Degree of pollution	3
Rated surge voltage	1.5 kV

Contact: Contact group 2

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Nominal current I_N	8 A
Overvoltage category	II
Degree of pollution	3

Connection data

Connection method	Crimp connection
-------------------	------------------

Material specifications

Material Insulating body	PA 6.6
--------------------------	--------

Connector

RC-1RS1NRA0000 - Contact insert




1603213

<https://www.phoenixcontact.com/us/products/1603213>

Direction of rotation	Standard
-----------------------	----------

Drawings

Schematic diagram



Connector pin assignment

RC-1RS1NRA0000 - Contact insert



1603213

<https://www.phoenixcontact.com/us/products/1603213>

Classifications

ECLASS

ECLASS-13.0	27440223
-------------	----------

UNSPSC

UNSPSC 21.0	39121522
-------------	----------

RC-1RS1NRA0000 - Contact insert



1603213

<https://www.phoenixcontact.com/us/products/1603213>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com