


DF-PTMC-2-ZB - Marker adapter



3270406

<https://www.phoenixcontact.com/us/products/3270406>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker adapter, for accommodating the marking, depth: 13 mm, width: 8.5 mm, height: 30 mm, color: gray

Your advantages

- Easy marking options
- Accessories for snapping on to PTMC
- For lateral latching on to PTMC
- Enables the creation of a marking matrix

Commercial data

Item number	3270406
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE69
Product key	BE6ZWX
GTIN	4055626314938
Weight per piece (including packing)	2.07 g
Weight per piece (excluding packing)	1.82 g
Customs tariff number	39269097
Country of origin	PL

DF-PTMC-2-ZB - Marker adapter



3270406

<https://www.phoenixcontact.com/us/products/3270406>

Technical data

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Width	8.5 mm
Height	30 mm
Depth	13 mm

Material specifications

Color	gray (RAL 7042)
Material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

DF-PTMC-2-ZB - Marker adapter



3270406

<https://www.phoenixcontact.com/us/products/3270406>

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

ETIM

ETIM 9.0	EC004591
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

DF-PTMC-2-ZB - Marker adapter



3270406

<https://www.phoenixcontact.com/us/products/3270406>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com