

UM-BEFE 35 - Base element

2955564

<https://www.phoenixcontact.com/us/products/2955564>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Base element with snap-on foot, for mounting on NS 32 or NS 35/7.5 DIN rail, with ribs, L = 35 mm



Commercial data

Item number	2955564
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDDA
GTIN	4017918085537
Weight per piece (including packing)	21.18 g
Weight per piece (excluding packing)	21.18 g
Customs tariff number	85389099
Country of origin	PL

UM-BEFE 35 - Base element

2955564

<https://www.phoenixcontact.com/us/products/2955564>




Technical data

Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM BE
Ventilation openings present	no

Dimensions

Dimensional drawing	
Width	35 mm
Height	111 mm
Depth	27.7 mm

Material specifications

Color (Housing)	green (RAL 6021)
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	DIN rail mounting
---------------	-------------------


UM-BEFE 35 - Base element

2955564

<https://www.phoenixcontact.com/us/products/2955564>



Drawings




UM-BEFE 35 - Base element

2955564

<https://www.phoenixcontact.com/us/products/2955564>



Dimensional drawing



UM-BEFE 35 - Base element



2955564

<https://www.phoenixcontact.com/us/products/2955564>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2955564>



UL Recognized

Approval ID: E240868

UM-BEFE 35 - Base element



2955564

<https://www.phoenixcontact.com/us/products/2955564>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-BEFE 35 - Base element



2955564
<https://www.phoenixcontact.com/us/products/2955564>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com