

# UM-BE 35 GY - Base element

2958778

<https://www.phoenixcontact.com/us/products/2958778>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, DIN rail mounting, Plug-in module base element



## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2958778                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | ACHDDA                         |
| GTIN                                 | 4017918279912                  |
| Weight per piece (including packing) | 20 g                           |
| Weight per piece (excluding packing) | 20 g                           |
| Country of origin                    | PL                             |

# UM-BE 35 GY - Base element

2958778

<https://www.phoenixcontact.com/us/products/2958778>



## Technical data

### Product properties

|                              |                              |
|------------------------------|------------------------------|
| Product type                 | Component housing lower part |
| Housing type                 | Press-drawn section housings |
| Housing series               | UM                           |
| Product family               | UM BE                        |
| Ventilation openings present | no                           |

### Material specifications

|                         |                 |
|-------------------------|-----------------|
| Color (Housing)         | gray (RAL 7042) |
| Housing material        | PA              |
| Surface characteristics | untreated       |

### Environmental and real-life conditions

#### Ambient conditions

|   |  |
|---|--|
| Ambient temperature (operation)         | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                   |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                   |
| Relative humidity (storage/transport)   | 80 %   |

### Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

# UM-BE 35 GY - Base element

2958778

<https://www.phoenixcontact.com/us/products/2958778>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2958778>



**UL Recognized**

Approval ID: E240868

# UM-BE 35 GY - Base element



2958778

<https://www.phoenixcontact.com/us/products/2958778>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190601 |
| ECLASS-15.0 | 27190601 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# UM-BE 35 GY - Base element



2958778  
<https://www.phoenixcontact.com/us/products/2958778>

## Environmental product compliance

|   |  |
|---|--|
| EU RoHS                                 |  |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |  |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|   | No hazardous substances above the limits |
| EU REACH SVHC                           |  |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)