

# CUTFOX 45 - Cable-cutting tool



1212132

<https://www.phoenixcontact.com/us/products/1212132>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Two-hand ring cable cutter, with ratchet function, for copper and aluminum up to 45 mm diameter (up to 300 mm<sup>2</sup>)

## Your advantages

- Unlockable
- Clean and precise cuts, even with thicker cables
- Less effort required due to the ratchet mechanism
- Ergonomic handle design to eliminate fatigue when working

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212132       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3111        |
| GTIN                                 | 4046356454117 |
| Weight per piece (including packing) | 1,096.5 g     |
| Weight per piece (excluding packing) | 1,028.7 g     |
| Customs tariff number                | 82034000      |
| Country of origin                    | DE            |

# CUTFOX 45 - Cable-cutting tool

1212132

<https://www.phoenixcontact.com/us/products/1212132>



## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

|                  |                                 |
|------------------|---------------------------------|
| Product type     | Cutting tool                    |
| Application      | Aluminum                        |
|                  | Copper                          |
| Product property | Effort-saving ratchet mechanism |
|                  | Ring cutter                     |
|                  | One-hand cutter                 |
|                  | Mechanism that can be released  |

### Dimensions

|          |        |
|----------|--------|
| Width    | 110 mm |
| Length   | 260 mm |
| Diameter | 45 mm  |

### Material specifications

|       |              |
|-------|--------------|
| Color | multicolored |
|-------|--------------|

### Cable/line

|                         |            |
|-------------------------|------------|
| External cable diameter | ≤ 45.00 mm |
|-------------------------|------------|

# CUTFOX 45 - Cable-cutting tool

1212132

<https://www.phoenixcontact.com/us/products/1212132>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212132>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CUTFOX 45 - Cable-cutting tool



1212132

<https://www.phoenixcontact.com/us/products/1212132>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21044701 |
| ECLASS-15.0 | 21044701 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000142 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CUTFOX 45 - Cable-cutting tool



1212132

<https://www.phoenixcontact.com/us/products/1212132>

## Environmental product compliance

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                     |
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
| EU REACH SVHC                           |                                                                                     |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                          |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)