

WP-BASE C PA HF 42,5 BK - Hose holder with cover



3240964

<https://www.phoenixcontact.com/us/products/3240964>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hose holder with cover, material: PA, color: black, flammability rating in acc. with UL 94: V2

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240964 |
| Packing unit | 25 pc |
| Minimum order quantity | 25 pc |
| Sales key | BF68 |
| Product key | AF7DSA |
| GTIN | 4046356710725 |
| Weight per piece (including packing) | 23.43 g |
| Weight per piece (excluding packing) | 23.43 g |
| Customs tariff number | 39174000 |
| Country of origin | DE |

WP-BASE C PA HF 42,5 BK - Hose holder with cover



3240964

<https://www.phoenixcontact.com/us/products/3240964>

Technical data

Product properties

| | |
|--------------|-------------------|
| Product type | Mounting material |
|--------------|-------------------|

Dimensions

| | |
|---------------|---------|
| Diameter | 42.5 mm |
| Hole diameter | 6.5 mm |

Material specifications

| | |
|--|--------------|
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Components | halogen-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

Mounting

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

WP-BASE C PA HF 42,5 BK - Hose holder with cover



3240964

<https://www.phoenixcontact.com/us/products/3240964>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 27430315 |
| ECLASS-13.0 | 27430315 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000799 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31162900 |
|-------------|----------|

WP-BASE C PA HF 42,5 BK - Hose holder with cover



3240964

<https://www.phoenixcontact.com/us/products/3240964>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com