

VS-PPC-C2-PC-ROBK-L-WB - Insulating part



1402973

<https://www.phoenixcontact.com/us/products/1402973>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insulating part, degree of protection: IP65/IP67, color: black

Your advantages

- Compatible with IP67 panel-mount frame
- Safe operation with the right degree of protection
- Robust industrial design

Commercial data

Item number	1402973
Packing unit	100 pc
Minimum order quantity	100 pc
Product key	ABNOJZ
GTIN	4046356637732
Weight per piece (including packing)	7.905 g
Weight per piece (excluding packing)	9.006 g
Country of origin	DE

VS-PPC-C2-PC-ROBK-L-WB - Insulating part



1402973

<https://www.phoenixcontact.com/us/products/1402973>

Technical data

Product properties

Product type	Protective cover
Type	Version 14

Dimensions

Width	34 mm
Height	22.6 mm
Length	20.9 mm

Material specifications

Color	black
Material	Plastic
Flammability rating according to UL 94	V0
Seal material	NBR

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

VS-PPC-C2-PC-ROBK-L-WB - Insulating part

1402973

<https://www.phoenixcontact.com/us/products/1402973>



Drawings

VS-PPC-C2-PC-ROBK-L-WB - Insulating part



1402973

<https://www.phoenixcontact.com/us/products/1402973>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-PPC-C2-PC-ROBK-L-WB - Insulating part



1402973

<https://www.phoenixcontact.com/us/products/1402973>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com