

# NS 35/ 7,5 BLK UNPERF 2000MM - DIN rail, unperforated



0801775

<https://www.phoenixcontact.com/us/products/0801775>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, uncoated, Standard profile, color: silver-colored

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0801775       |
| Packing unit                         | 25 m          |
| Minimum order quantity               | 50 m          |
| Sales key                            | BE72          |
| Product key                          | BE7231        |
| GTIN                                 | 4017918155445 |
| Weight per piece (including packing) | 714 g         |
| Weight per piece (excluding packing) | 714 g         |
| Customs tariff number                | 72166190      |
| Country of origin                    | DE            |

# NS 35/ 7,5 BLK UNPERF 2000MM - DIN rail, unperforated



0801775


<https://www.phoenixcontact.com/us/products/0801775>

## Technical data

### Product properties

|              |          |
|--------------|----------|
| Product type | DIN rail |
|--------------|----------|

### Dimensions

|                     |                                                                                   |
|---------------------|-----------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 35 mm                                                                             |
| Depth               | 7.5 mm                                                                            |
| Length              | 2000 mm                                                                           |

### Material specifications

|          |                |
|----------|----------------|
| Color    | silver-colored |
| Material | Steel          |
| Coating  | uncoated       |

### Standards and regulations

|                                  |                  |
|----------------------------------|------------------|
| Connection in acc. with standard | IEC / EN         |
| Tests                            | acc. to EN 60715 |

# NS 35/ 7,5 BLK UNPERF 2000MM - DIN rail, unperforated





0801775

<https://www.phoenixcontact.com/us/products/0801775>

## Drawings

Dimensional drawing



# NS 35/ 7,5 BLK UNPERF 2000MM - DIN rail, unperforated



0801775

<https://www.phoenixcontact.com/us/products/0801775>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400602 |
| ECLASS-15.0 | 27400602 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001285 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

# NS 35/ 7,5 BLK UNPERF 2000MM - DIN rail, unperforated



0801775

<https://www.phoenixcontact.com/us/products/0801775>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)