

ZB 25 CUS - Zack marker strip



0802752

<https://www.phoenixcontact.com/us/products/0802752>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 25 mm, Number of individual labels: 4, text field height: 10 mm, text field width: 25 mm

Commercial data

Item number	0802752
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8112
GTIN	4046356858496
Weight per piece (including packing)	2.38 g
Weight per piece (excluding packing)	2.38 g
Country of origin	PL

ZB 25 CUS - Zack marker strip



0802752

<https://www.phoenixcontact.com/us/products/0802752>

Technical data

Product properties

Product type	Klemmenmarker
Pitch	25 mm

Marking

Number of individual labels	4
Number of individual labels per row	4
Number of marker strips	4

Dimensions

Width	25.10 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	25 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	snap into tall marker groove
---------------	------------------------------

ZB 25 CUS - Zack marker strip

0802752

<https://www.phoenixcontact.com/us/products/0802752>



Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 25 CUS - Zack marker strip



0802752
<https://www.phoenixcontact.com/us/products/0802752>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com