

CARRIER-TM 300 - Marker carriers



0828282

<https://www.phoenixcontact.com/us/products/0828282>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker adapter, 300 mm in length, for manual cutting, can be engaged in a flat marker groove, for ZB ..., UC-TM ... or UCT-TM ...

Your advantages

- For accommodating ZB ..., UC-TM ... or UCT-TM ... terminal markers which increases the labeling area
- Can be snapped into all terminal blocks in the CLIPLINE complete system that have a flat lateral marker groove

Commercial data

Item number	0828282
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BG12
Product key	BG211A
GTIN	4046356478526
Weight per piece (including packing)	6.211 g
Weight per piece (excluding packing)	5.5 g
Customs tariff number	39269097
Country of origin	DE

CARRIER-TM 300 - Marker carriers



0828282

<https://www.phoenixcontact.com/us/products/0828282>

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	300.00 mm
Height	9.93 mm
Depth	6.10 mm

Material specifications

RoHS compliant	yes
Color	gray (RAL 7042)
Material	PA
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	latching
---------------	----------

CARRIER-TM 300 - Marker carriers



0828282

<https://www.phoenixcontact.com/us/products/0828282>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 9.0	EC002248
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CARRIER-TM 300 - Marker carriers



0828282

<https://www.phoenixcontact.com/us/products/0828282>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com