

RC-0000000C3FZ - Housing for circular connector



1618189

<https://www.phoenixcontact.com/us/products/1618189>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing for circular connector, series: RC, straight, Screw locking mechanism, M23, Radial O-ring, shielded: yes, panel thickness max.: 2.5 mm

Commercial data

Item number	1618189
Packing unit	20 pc
Minimum order quantity	60 pc
Note	Made to order (non-returnable)
Product key	ABRAFL
GTIN	4046356952583
Weight per piece (including packing)	83.09 g
Weight per piece (excluding packing)	83.09 g
Country of origin	DE

RC-0000000C3FZ - Housing for circular connector



1618189

<https://www.phoenixcontact.com/us/products/1618189>

Technical data

Notes

Order information:	Order contact inserts and cable clamping/shield accessories separately
--------------------	--

Product properties

Product type	Circular connector housing
Series	RC
Application	Signal
Shielded	yes
Thread type	M23

Dimensions

Panel thickness	< 2.5 mm
-----------------	----------

Material specifications

Housing material	Metal
------------------	-------

Connector

Type	straight
------	----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

Mounting

Mounting type	Rear mounting/square flange (4x M3)
---------------	-------------------------------------

RC-0000000C3FZ - Housing for circular connector



1618189

<https://www.phoenixcontact.com/us/products/1618189>

Classifications

ECLASS

ECLASS-13.0	27440224
-------------	----------

UNSPSC

UNSPSC 21.0	39121421
-------------	----------

RC-0000000C3FZ - Housing for circular connector



1618189

<https://www.phoenixcontact.com/us/products/1618189>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com