

# WIREFOX-D CX-5 - Stripping tool

1212167

<https://www.phoenixcontact.com/us/products/1212167>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stripping tool for coaxial cables of Ø 2.5 ... 7.6 mm, 3-level, strip-off dimensions 5.5 and 5.5 mm

## Your advantages

- Large selection of precision stripping tools
- The right tool for every application

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212167       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3122        |
| GTIN                                 | 4046356454353 |
| Weight per piece (including packing) | 78 g          |
| Weight per piece (excluding packing) | 78 g          |
| Customs tariff number                | 82032000      |
| Country of origin                    | SE            |

# WIREFOX-D CX-5 - Stripping tool

1212167

<https://www.phoenixcontact.com/us/products/1212167>



## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

|                    |                                                    |
|--------------------|----------------------------------------------------|
| Product type       | Stripping tool                                     |
| Application        | Standard                                           |
|                    | Koaxialkabel                                       |
| Special properties | 3-stage Strip-off dimension l1= 5.5 mm, l2= 5.5 mm |
| Product property   | Stripping commercially available coaxial cables    |
|                    | Replaceable stripping blade                        |
|                    | Multi-stage stripping in just one step             |

### Connection data

#### Conductor connection

|                             |                 |
|-----------------------------|-----------------|
| Cross section range, metric | 0 mm² ... 0 mm² |
| Stripping length            | 5.5 mm          |

### Dimensions

|        |         |
|--------|---------|
| Width  | 25.5 mm |
| Height | 37.5 mm |
| Length | 90 mm   |

### Material specifications

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

### Cable/line

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 2.5 mm ... 7.6 mm |
|-------------------------|-------------------|

# WIREFOX-D CX-5 - Stripping tool



1212167

<https://www.phoenixcontact.com/us/products/1212167>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212167>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# WIREFOX-D CX-5 - Stripping tool



1212167

<https://www.phoenixcontact.com/us/products/1212167>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043706 |
| ECLASS-15.0 | 21043706 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002109 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# WIREFOX-D CX-5 - Stripping tool



1212167  
<https://www.phoenixcontact.com/us/products/1212167>

## Environmental product compliance

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                     |
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
| EU REACH SVHC                           |                                                                                     |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                          |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)