

PDC-4PT-138MS-FS/MINFS - T distributor



1527831

<https://www.phoenixcontact.com/us/products/1527831>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



T distributor, 4-position, Plug straight, on Socket straight and Socket straight 7/8"-16UNF, coding: A

Commercial data

Item number	1527831
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF14
Product key	AF1INB
GTIN	4063151998110
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	MX

PDC-4PT-138MS-FS/MINFS - T distributor



1527831

<https://www.phoenixcontact.com/us/products/1527831>

Technical data

Product properties

Product type	T-distributor
Application	Energy supply
Number of positions	4
Shielded	no

Electrical properties

Nominal voltage U_N	600 V AC (UL rating)
	50 V AC (IEC rating)
Nominal current I_N	25 A (15A drop 7/8" connector)

Material specifications

Material	Anodized aluminum
Flammability rating according to UL 94	V0
Material of grip body	Thermoplastic
Contact material	CuZn
Contact surface material	Au
Contact carrier material	Thermoplastic

Connector

Connection 2

Type	Socket straight
------	-----------------

Connection 3

Type	Socket straight 7/8"-16UNF
Coding type	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 90 °C (Plug / socket)

Standards and regulations

Standards/specifications	UL 2237
Note	SCCR 65KA
Standard designation	Vibration
Standards/specifications	MIL-STD-202 method 204
Standard designation	Thermal shock
Standards/specifications	MIL-STD-202 method 207
Standard designation	48 hour salt spray
Standards/specifications	MIL-STD-202 method 101


PDC-4PT-138MS-FS/MINFS - T distributor



1527831


<https://www.phoenixcontact.com/us/products/1527831>

Drawings




1-3/8" / 7/8" T-distributor

Schematic diagram




Pin assignment, plug, 1-3/8"-16UNF, 4-pos., view of male side

Schematic diagram



Pin assignment, socket, 1-3/8"-16UNF, 4-pos., view of female side

Schematic diagram



Pin assignment, socket, 7/8"-16UNF, 4-pos., view of female side


PDC-4PT-138MS-FS/MINFS - T distributor



1527831

<https://www.phoenixcontact.com/us/products/1527831>

Circuit diagram



Contact assignment

PDC-4PT-138MS-FS/MINFS - T distributor



1527831

<https://www.phoenixcontact.com/us/products/1527831>

Classifications

ECLASS

ECLASS-13.0	27440106
ECLASS-15.0	27440106

ETIM

ETIM 9.0	EC002925
----------	----------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com