

UC-17P1N12RLDU - Cable connector



1619127

<https://www.phoenixcontact.com/us/products/1619127>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Pin, Solder cup, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1619127
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAIA
GTIN	4046356983594
Weight per piece (including packing)	128.41 g
Weight per piece (excluding packing)	123.273 g
Country of origin	DE

UC-17P1N12RLDU - Cable connector



1619127

<https://www.phoenixcontact.com/us/products/1619127>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Number Contact (Contact group 1)	17
Diameter Contact (Contact group 1)	1 mm
Litz wire cross-section min. Contact (Contact group 1)	0.08 mm ²
Litz wire cross-section max. Contact (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

UC-17P1N12RLDU - Cable connector


1619127

<https://www.phoenixcontact.com/us/products/1619127>



Drawings

Schematic diagram



Connector pin assignment


UC-17P1N12RLDU - Cable connector

1619127

<https://www.phoenixcontact.com/us/products/1619127>



Schematic diagram




Connector pin assignment

UC-17P1N12RLDU - Cable connector

1619127

<https://www.phoenixcontact.com/us/products/1619127>

Schematic diagram



Dimensional drawing

UC-17P1N12RLDU - Cable connector



1619127

<https://www.phoenixcontact.com/us/products/1619127>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UC-17P1N12RLDU - Cable connector



1619127

<https://www.phoenixcontact.com/us/products/1619127>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2c55bfd1-9924-41aa-ae0c-0127e0d9261e

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com