

CES-B10-WRG-BK - Flat gasket



0801725

<https://www.phoenixcontact.com/us/products/0801725>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Flat gasket made of NBR, size B10



Commercial data

Item number	0801725
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF67
Product key	AF7CZX
GTIN	4046356675246
Weight per piece (including packing)	10.45 g
Weight per piece (excluding packing)	9.73 g
Customs tariff number	40169300
Country of origin	DE

CES-B10-WRG-BK - Flat gasket

0801725

<https://www.phoenixcontact.com/us/products/0801725>



Technical data

Product properties

Product type	Seal
Type	B10

Dimensions

Dimensional drawing	
Width	57.5 mm
Height	2.5 mm
Length	99.2 mm
Drill hole distance, horizontal	83 mm
Drill hole distance, vertical	32 mm
Hole diameter	4.5 mm

Material specifications

Seal material	NBR
---------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C (static)
---------------------------------	---------------------------

CES-B10-WRG-BK - Flat gasket


0801725

<https://www.phoenixcontact.com/us/products/0801725>



Drawings

Dimensional drawing



Dimensional drawing

CES-B10-WRG-BK - Flat gasket



0801725

<https://www.phoenixcontact.com/us/products/0801725>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0801725>

DNV

Approval ID: TAE00003VJ

CES-B10-WRG-BK - Flat gasket



0801725

<https://www.phoenixcontact.com/us/products/0801725>

Classifications

ECLASS

ECLASS-13.0	23071590
ECLASS-15.0	23071590

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	31401600
-------------	----------

CES-B10-WRG-BK - Flat gasket



0801725
<https://www.phoenixcontact.com/us/products/0801725>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.409 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com