

KLM-A + ESL 44X7 - Terminal strip marker carrier



0809421

<https://www.phoenixcontact.com/us/products/0809421>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Terminal strip markers and insert strips ESL..., adjustable height, for use with end clamps E/UK, E/NS 35 N or CLIPFIX 35, lettering field of the insert strip: 44 x 7 mm

Commercial data

Item number	0809421
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG12
Product key	BG211A
GTIN	4017918201821
Weight per piece (including packing)	2.12 g
Weight per piece (excluding packing)	2.206 g
Customs tariff number	39269097
Country of origin	DE

KLM-A + ESL 44X7 - Terminal strip marker carrier



0809421

<https://www.phoenixcontact.com/us/products/0809421>

Technical data

Notes

General	Print image may vary depending on laser printer
---------	---

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	9.50 mm
Height	46.00 mm
Depth	36.80 mm

Material specifications

Color	transparent
Flammability rating according to UL 94	HB
Base element material	ABS
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Mounting

Mounting type	plug in
---------------	---------

KLM-A + ESL 44X7 - Terminal strip marker carrier



0809421

<https://www.phoenixcontact.com/us/products/0809421>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 9.0	EC002248
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

KLM-A + ESL 44X7 - Terminal strip marker carrier



0809421
<https://www.phoenixcontact.com/us/products/0809421>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com