

WP-SC PA HF 42,5 BK - Cable protection end sleeve



3240987

<https://www.phoenixcontact.com/us/products/3240987>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable protection end sleeve, material: PA 6, color: black, flammability rating in acc. with UL 94: V2, inside diameter: 33.8 mm

Commercial data

Item number	3240987
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356711050
Weight per piece (including packing)	6.432 g
Weight per piece (excluding packing)	6.336 g
Customs tariff number	39174000
Country of origin	DE

WP-SC PA HF 42,5 BK - Cable protection end sleeve



3240987

<https://www.phoenixcontact.com/us/products/3240987>

Technical data

Product properties

Product type	Protective cap
--------------	----------------

Dimensions

Length	25 mm
Diameter	42.5 mm

Internal dimensions

Internal diameter	33.8 mm
-------------------	---------

Material specifications

Material	PA 6
Flammability rating according to UL 94	V2
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

WP-SC PA HF 42,5 BK - Cable protection end sleeve



3240987

<https://www.phoenixcontact.com/us/products/3240987>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240987>



LR

WP-SC PA HF 42,5 BK - Cable protection end sleeve



3240987

<https://www.phoenixcontact.com/us/products/3240987>

Classifications

ECLASS

ECLASS-15.0	27430316
ECLASS-13.0	27430316

ETIM

ETIM 9.0	EC000519
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

WP-SC PA HF 42,5 BK - Cable protection end sleeve



3240987

<https://www.phoenixcontact.com/us/products/3240987>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com