

0800446:=  
<https://www.phoenixcontact.com/us/products/0800446>:=

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, horizontally labeled with the symbol: Symbols, suitable for diameters 1.4 ... 2.5 mm, yellow, mounting type: slide-on

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0800446:=     |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Product key                          | BG222B        |
| GTIN                                 | 4017918909017 |
| Weight per piece (including packing) | 60 MGM        |
| Weight per piece (excluding packing) | 60 MGM        |
| Country of origin                    | PL            |

# PMH 0:SYMBOLE = - Wire marking tag



0800446:=

<https://www.phoenixcontact.com/us/products/0800446>:=

## Technical data

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

### Marking

|          |         |
|----------|---------|
| Printing | Symbols |
|----------|---------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 3.2 mm  |
| Length | 4.50 mm |

### External dimensions

|                  |                   |
|------------------|-------------------|
| Outside diameter | 1.4 mm ... 2.5 mm |
|------------------|-------------------|

### Text field

|                   |         |
|-------------------|---------|
| Text field width  | 3.20 mm |
| Text field height | 2.60 mm |

### Material specifications

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Color                                  | yellow (RAL 1018)                        |
| Material                               | Ethylene-vinyl acetate (EVA)             |
| Flammability rating according to UL 94 | V0                                       |
| Components                             | free from silicone, halogen, and cadmium |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Mounting

|               |          |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

# PMH 0:SYMBOLE = - Wire marking tag



0800446:=  
<https://www.phoenixcontact.com/us/products/0800446>:=

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001530 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)