

EA 5 - Cover



1024014

<https://www.phoenixcontact.com/us/products/1024014>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover, material: ABS, color: transparent



Your advantages

- Can be labeled with EML (24X3)R
- Protection against environmental influences
- Protection against accidental actuation of terminal points or disconnect terminal blocks
- Covering of live parts

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1024014 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BE07 |
| Product key | BE7124 |
| GTIN | 4017918015268 |
| Weight per piece (including packing) | 0.88 g |
| Weight per piece (excluding packing) | 0.873 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Cover profile |
|--------------|---------------|

Connection data

Cable lug connection

| | |
|-------------------------|-------------------------|
| Cross section range AWG | (converted acc. to IEC) |
|-------------------------|-------------------------|

Dimensions

| | |
|--------|---------|
| Width | 5 mm |
| Height | 50 mm |
| Depth | 17.5 mm |
| Length | 50 mm |

Material specifications

| | |
|----------------------------------------|--------------------------------|
| Color | transparent |
| Material | ABS |
| Flammability rating according to UL 94 | HB |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 80 °C |
|---------------------------------|------------------|

1024014

<https://www.phoenixcontact.com/us/products/1024014>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281107 |
| ECLASS-15.0 | 27281107 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001777 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121100 |
|-------------|----------|

Environmental product compliance

| | |
|-----------------------------------------|------------------------------------------|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com