

# NS 35/15 AL UNP 755MM - DIN rail, unperforated



1207661

<https://www.phoenixcontact.com/us/products/1207661>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail, unperforated, similar to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver-colored

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1207661       |
| Packing unit                         | 20 pc         |
| Minimum order quantity               | 20 pc         |
| Product key                          | BH8422        |
| GTIN                                 | 4046356366595 |
| Weight per piece (including packing) | 999 g         |
| Weight per piece (excluding packing) | 999 g         |
| Country of origin                    | AT            |

# NS 35/15 AL UNP 755MM - DIN rail, unperforated



1207661


<https://www.phoenixcontact.com/us/products/1207661>

## Technical data

## Product properties

|              |          |
|--------------|----------|
| Product type | DIN rail |
|--------------|----------|

## Dimensions

|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 35 mm                                                                              |
| Hole width          | 0 mm                                                                               |
| Height              | 15 mm                                                                              |
| Hole height         | 0 mm                                                                               |
| Length              | 755 mm                                                                             |
| Drill hole spacing  | 0 mm                                                                               |

## Material specifications

|          |                |
|----------|----------------|
| Color    | silver-colored |
| Material | Aluminum       |
| Coating  | uncoated       |

## Standards and regulations

|       |                     |
|-------|---------------------|
| Tests | similar to EN 60715 |
|-------|---------------------|


# NS 35/15 AL UNP 755MM - DIN rail, unperforated

1207661

<https://www.phoenixcontact.com/us/products/1207661>



## Drawings



# NS 35/15 AL UNP 755MM - DIN rail, unperforated



1207661

<https://www.phoenixcontact.com/us/products/1207661>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400602 |
| ECLASS-15.0 | 27400602 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001285 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

# NS 35/15 AL UNP 755MM - DIN rail, unperforated



1207661

<https://www.phoenixcontact.com/us/products/1207661>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)