

# PROT-MINMS-PA-CHAIN - Screw plug

1430925

<https://www.phoenixcontact.com/us/products/1430925>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

7/8" sealing cap made of plastic with fixing band, for sensor cables, for 7/8" sockets



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1430925       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF46          |
| Product key                          | AF1ZAX        |
| GTIN                                 | 4046356332811 |
| Weight per piece (including packing) | 11.05 g       |
| Weight per piece (excluding packing) | 11 g          |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

# PROT-MINMS-PA-CHAIN - Screw plug



1430925

<https://www.phoenixcontact.com/us/products/1430925>

## Technical data

### Product properties

|              |                            |
|--------------|----------------------------|
| Product type | Plug for cable screw gland |
| Thread type  | 7/8"                       |

### Dimensions

|                     |       |
|---------------------|-------|
| Dimensional drawing |       |
| Diameter            | 27 mm |

### Material specifications

|  |                    |
|--|--------------------|
| Material                               | PUR (Holding band) |
| Flammability rating according to UL 94 | V0                 |
| Seal material                          | NBR                |
| Material for screw connection          | PA 6.6             |

### Environmental and real-life conditions

#### Ambient conditions

|   |                  |
|---|------------------|
| Degree of protection  | IP65             |
|   | IP67             |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C |

# PROT-MINMS-PA-CHAIN - Screw plug




1430925

<https://www.phoenixcontact.com/us/products/1430925>

## Drawings

Dimensional drawing



Dimensional drawing

# PROT-MINMS-PA-CHAIN - Screw plug



1430925

<https://www.phoenixcontact.com/us/products/1430925>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 23111190 |
| ECLASS-15.0 | 23111190 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000032 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# PROT-MINMS-PA-CHAIN - Screw plug



1430925

<https://www.phoenixcontact.com/us/products/1430925>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)