

# WIREFOX-D 16 - Stripping tool

1212173

<https://www.phoenixcontact.com/us/products/1212173>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stripping tool, for stripping lines (specially for fiber optics lines) of Ø 4 - 16 mm

## Your advantages

- Large selection of precision stripping tools
- The right tool for every application

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212173       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3123        |
| GTIN                                 | 4046356454278 |
| Weight per piece (including packing) | 119.9 g       |
| Weight per piece (excluding packing) | 119.8 g       |
| Customs tariff number                | 82055980      |
| Country of origin                    | DE            |

# WIREFOX-D 16 - Stripping tool

1212173

<https://www.phoenixcontact.com/us/products/1212173>



## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

|                  |                             |
|------------------|-----------------------------|
| Product type     | Stripping tool              |
| Application      | Standard                    |
| Product property | Freely movable blade        |
|                  | Replaceable stripping blade |

### Connection data

#### Conductor connection

|                             |                                          |
|-----------------------------|------------------------------------------|
| Cross section range, metric | 4 mm <sup>2</sup> ... 70 mm <sup>2</sup> |
| Cross section range AWG     | 12 ... 0                                 |
| Stripping length            | 100 mm                                   |

### Dimensions

|        |          |
|--------|----------|
| Width  | 34.4 mm  |
| Height | 28.7 mm  |
| Length | 131.5 mm |

### Material specifications

|       |                      |
|-------|----------------------|
| Color | multicolored (RAL -) |
|-------|----------------------|

### Cable/line

|                         |                |
|-------------------------|----------------|
| External cable diameter | 4 mm ... 16 mm |
|-------------------------|----------------|

# WIREFOX-D 16 - Stripping tool



1212173

<https://www.phoenixcontact.com/us/products/1212173>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212173>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# WIREFOX-D 16 - Stripping tool



1212173

<https://www.phoenixcontact.com/us/products/1212173>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043706 |
| ECLASS-15.0 | 21043706 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002109 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# WIREFOX-D 16 - Stripping tool



1212173

<https://www.phoenixcontact.com/us/products/1212173>

## Environmental product compliance

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                     |
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
| EU REACH SVHC                           |                                                                                     |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                          |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)