

OCS PANEL 0806 PC - Mounting panel



1471783

<https://www.phoenixcontact.com/us/products/1471783>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting panel for housing size of 8" x 6", material: polycarbonate, color: white



Your advantages

- Internationally certified housing system
- Special plastic enables safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1471783 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC04 |
| Product key | ACFDBZ |
| GTIN | 4063151881337 |
| Weight per piece (including packing) | 0.101 kg |
| Weight per piece (excluding packing) | 0.099 kg |
| Customs tariff number | 39269097 |
| Country of origin | DE |

OCS PANEL 0806 PC - Mounting panel



1471783

<https://www.phoenixcontact.com/us/products/1471783>

Technical data

Product properties

| | |
|----------------|-----------------|
| Product type | Mounting plate |
| Housing type | Outdoor housing |
| Housing series | OCS |
| Product family | OCS..0806.. |

Dimensions

| | |
|--------|--------|
| Width | 120 mm |
| Height | 171 mm |
| Depth | 4 mm |

Material specifications

| | |
|--|------------------|
| Color | white (RAL 9010) |
| Material | PC |
| Flammability rating according to UL 94 | HB |
| Insulating material | PC |
| Surface characteristics | untreated |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 80 °C |
|---------------------------------|------------------|

Mounting

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Packaging specifications

| | |
|-------------------|------|
| Type of packaging | none |
|-------------------|------|

OCS PANEL 0806 PC - Mounting panel

1471783

<https://www.phoenixcontact.com/us/products/1471783>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1471783>

FI Cert

Approval ID: FI/42054

OCS PANEL 0806 PC - Mounting panel



1471783

<https://www.phoenixcontact.com/us/products/1471783>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

OCS PANEL 0806 PC - Mounting panel



1471783

<https://www.phoenixcontact.com/us/products/1471783>

Environmental product compliance

| | |
|---|--|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com