

SF-SL 0,6X3,5-100 - Screwdriver



1212549

<https://www.phoenixcontact.com/us/products/1212549>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screwdriver, bladed (lasered), size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

Your advantages

- The tools feature ergonomic two-component safety handles
- Large contact surface of blades inside screw head

Commercial data

Item number	1212549
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3141
GTIN	4046356589840
Weight per piece (including packing)	36.1 g
Weight per piece (excluding packing)	35.7 g
Customs tariff number	82054000
Country of origin	CZ

SF-SL 0,6X3,5-100 - Screwdriver



1212549

<https://www.phoenixcontact.com/us/products/1212549>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Screwdriver tools

Type

Bladed

Connection data

Output

Bladed

Dimensions

Width

26 mm

Blade width

3.5 mm

Blade height

100 mm

Length

181 mm

Wrench size

0 mm

Wrench size for mounting

0 mm

Blade thickness

0.6 mm

Material specifications

Material

alloyed tool steel

Standards and regulations

Tests

DIN/ISO 2380-1

SF-SL 0,6X3,5-100 - Screwdriver



1212549

<https://www.phoenixcontact.com/us/products/1212549>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212549>



EAC

Approval ID: RU C-DE.AI30.B.01750

SF-SL 0,6X3,5-100 - Screwdriver



1212549

<https://www.phoenixcontact.com/us/products/1212549>

Classifications

ECLASS

ECLASS-13.0	21040407
ECLASS-15.0	21040407

ETIM

ETIM 9.0	EC000158
----------	----------

UNSPSC

UNSPSC 21.0	27111700
-------------	----------

SF-SL 0,6X3,5-100 - Screwdriver



1212549

<https://www.phoenixcontact.com/us/products/1212549>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com